



外形図 Outline drawing
 Renesasコード PTSB0044GH-A


RDK-G-001695-1 1/1

ルネサス エレクトロニクス株式会社
 Renesas Electronics Corporation

JEITA Package code	RENESAS code	MASS(TYP.) [g]
P-TSOP(2)44-10.16x18.41-0.80	PTSB0044GH-A	0.45



NOTE)
 1. DIMENSIONS "*1" AND "*2"
 DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION "*3" DOES NOT
 INCLUDE TRIM OFFSET.



Detail F

Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
D	18.313	18.41	18.517
E	10.058	10.16	10.262
A2	—	1.00	—
A1	0.05	0.10	0.15
A	—	—	1.194
bp	0.30	—	0.40
c	0.12	—	0.21
θ	0°	—	5°
HE	11.735	11.837	11.938
e	—	0.80	—
x	—	—	0.20
y	—	—	0.10
z	—	0.805	—
Lp	0.406	0.50	0.597