

JEITA Package Code

RENESAS Code

Previous Code




MASS[Typ.]

P-TSSOP16-4.4x5-0.65


PTSP0016JB-A

TTP-16DAV

0.05g



Terminal cross section  
(Ni/Pd/Au plating)



Detail F

NOTE)

1. DIMENSIONS\*\*1 (Nom)\*AND\*\*2\* DO NOT INCLUDE MOLD FLASH.
2. DIMENSION\*\*3\*DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	5.0	5.3
E	—	4.40	—
A <sub>2</sub>	—	—	—
A <sub>1</sub>	0.03	0.07	0.10
A	—	—	1.10
b <sub>P</sub>	0.15	0.20	0.25
b <sub>1</sub>	—	—	—
c	0.10	0.15	0.20
c <sub>1</sub>	—	—	—
θ	0°	—	8°
H <sub>E</sub>	6.20	6.40	6.60
e	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z	—	—	0.65
L	0.4	0.5	0.6
L <sub>1</sub>	—	1.0	—