

JEITA Package Code

P-TSSOP20-4.4x6.5-0.65

RENESAS Code




PTSP0020JB-A

Previous Code


TTP-20DAV

MASS[Typ.]

0.07g



Terminal cross section  
(Ni/Pd/Au plating)



Detail F

NOTE)

1. DIMENSIONS\*1 (Nom)\*AND\*2\* DO NOT INCLUDE MOLD FLASH.
2. DIMENSION\*3\* DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	6.50	6.80
E	—	4.40	—
A <sub>2</sub>	—	—	—
A <sub>1</sub>	0.03	0.07	0.10
A	—	—	1.10
$b_p$	0.15	0.20	0.25
$b_1$	—	—	—
c	0.10	0.15	0.20
$c_1$	—	—	—
$\theta$	0°	—	8°
$H_E$	6.20	6.40	6.60
$e$	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z	—	—	0.65
L	0.4	0.5	0.6
$L_1$	—	1.0	—