


Terminal cross section  
(Ni/Pd/Au plating)



Detail F

NOTE)

1. DIMENSIONS\*1 (Nom)\*AND\*2\* DO NOT INCLUDE MOLD FLASH.
2. DIMENSION\*3\* DOES NOT INCLUDE TRIM OFFSET.

| Reference Symbol | Dimension in Millimeters |      |      |
|------------------|--------------------------|------|------|
|                  | Min                      | Nom  | Max  |
| D                | —                        | 7.80 | 8.10 |
| E                | —                        | 4.40 | —    |
| A <sub>2</sub>   | —                        | —    | —    |
| A <sub>1</sub>   | 0.03                     | 0.07 | 0.10 |
| A                | —                        | —    | 1.10 |
| b <sub>p</sub>   | 0.15                     | 0.20 | 0.25 |
| b <sub>1</sub>   | —                        | —    | —    |
| c                | 0.10                     | 0.15 | 0.20 |
| c <sub>1</sub>   | —                        | —    | —    |
| $\theta$         | 0°                       | —    | 8°   |
| H <sub>E</sub>   | 6.20                     | 6.40 | 6.60 |
| e                | —                        | 0.65 | —    |
| x                | —                        | —    | 0.13 |
| y                | —                        | —    | 0.10 |
| Z                | —                        | —    | 0.65 |
| L                | 0.4                      | 0.5  | 0.6  |
| L <sub>1</sub>   | —                        | 1.0  | —    |