



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	5.00	—
E	—	5.00	—
v	—	—	0.15
w	—	—	0.15
A	0.86	0.93	1.00
A_1	0.20	0.25	0.30
e	—	0.5	—
b	0.25	0.30	0.35
x	—	—	0.05
y	—	—	0.08
y_1	—	—	0.2
S_D	—	—	—
S_E	—	—	—
Z_D	—	0.5	—
Z_E	—	0.5	—