



84-PIN PLASTIC FLGA (7.5x7.5)



Detail of (A) part

Detail of (B) part

Detail of (C) part



ITEM	MILLIMETERS
D	7.50±0.10
E	7.50±0.10
w	0.20
e	0.65
A	0.83±0.07
b	0.35±0.05
x	0.08
y	0.10
y1	0.20
ZD	1.15
ZE	1.15

P84FC-65-CA4