




TOP VIEW





SIDE VIEW




BOTTOM VIEW



RECOMMENDED LAND PATTERN
 (PCB Top View, NSMD Design)



Detail A
 (Rotated 90° CW)



Detail C - C'

NOTES:

1. JEDEC compatible.
2. All dimensions are in mm and angles are in degrees.
3. Use ± 0.05 mm for the non-toleranced dimensions.
4. Numbers in () are for references only.
5. Pre-reflow solderball diameter is $\text{Ø}0.45$ mm.