





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	2/29/16	JH



DIMENSIONS	min	max
A	0.90	1.10
A1	0.05	0.15
A2	0.85	0.95
b	0.19	0.30
c	0.09	0.20
D	7.7	7.9
E	4.3	4.5
e	0.65nom	
HE	6.3	6.5
L	0.5	0.7
θ	0°	8°

* WITHOUT MOLD FLASH

1. WEIGHT ≤ 0.09 g
2. BODY MATERIAL LOW STRESS EPOXY
3. LEAD MATERIAL Cu-ALLOY
4. LEAD FINISH SOLDER PLATING
5. LEAD FORM Z-BENDS
6. LEAD FORM Z-BENDS

TOLERANCES UNLESS SPECIFIED			
DECIMAL	ANGULAR	8024 Silver Creek Valley Rd San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-3572	
XXXX±	±	WWW.IDT.COM	
APPROVALS	DATE	TITLE PGG24 PACKAGE OUTLINE	
DRAWN	DATE	SIZE C DRAWING No. PSC-4056-03	
CHECKED		DO NOT SCALE DRAWING	
		SHEET 1 OF 1	