

ISL71590SEH, ISL73590SEH

Single-Event Effects (SEE)

AN1894

Rev 1.00

November 17, 2016

Introduction

The intense proton and heavy ion environment encountered in space applications can cause a variety of destructive and nondestructive single-event effects in electronic circuitry, including Single-Event Upset (SEU), Single-Event Transient (SET), Single-Event Functional Interrupt (SEFI), and Single-Event Burnout (SEB). SEE can lead to system-level performance issues including disruption, degradation, and destruction. For predictable and reliable space system operation, individual electronic components must be characterized to determine their SEE response. This report discusses the results of destructive SEE testing performed on the ISL71590SEH two-terminal temperature transducer. These results also apply to the ISL73590SEH.

Product Description

The ISL71590SEH is a radiation-hardened two-terminal temperature transducer. It has a high impedance current output that allows it to be insensitive to voltage drops across long lines. When provided a voltage between 4V and 33V on the input pin, the device acts as a constant current generator with a scale factor of $1\mu\text{A}/\text{K}$. The ISL71590SEH can operate across the -55°C to $+150^\circ\text{C}$ temperature range without the need of additional circuitry, and produces results with $\pm 1.7^\circ\text{C}$ accuracy over that temperature range. The absolute maximum supply voltage is 40V while the maximum operational supply voltage for in-spec operation is 33V, and this value is also 33V for operation in the heavy ion environment ('in-beam'). The part features notable low dose rate total dose hardness, with a maximum accuracy error of -1.0°C after 50krad(Si) at low dose rate.

With power requirements as low as 1.5mW (5V at 25°C), the part is a good choice for payload and booster temperature sensing as any well-insulated twisted pair cable will allow for proper operation. It can be used in several applications including temperature compensation networks, laser diode temperature compensation, sensor bias and linearization functions, and Proportional-to-Absolute Temperature (PTAT) biasing. The high output impedance ($>10\text{M}\Omega$) leaves plenty of room for variations in the power supply voltage. The part is electrically durable as it can withstand a forward voltage of 40V outside of the heavy ion environment (with a 33V maximum in-beam rating) and a reverse voltage of -40V. The case to lead breakdown voltage is $>200\text{V}$. The ISL71590SEH is available in a 2 Ld hermetically sealed flatpack. Key features of the part follow.

Features

- Minimal accuracy shift over low dose rate irradiation -1.5°C maximum
- Linear output current. $1.0\mu\text{A}/\text{K}$
- Wide power supply range 4V to 33V
- Low power consumption 1.5mW at 5V supply
- Operating temperature range. -55°C to $+125^\circ\text{C}$
- SEL/SEB threshold LET $86.4\text{MeV}\cdot\text{cm}^2/\text{mg}$
- Total dose tolerance, high dose rate 300krad(Si)
- Total dose tolerance, low dose rate 50krad(Si)
- QML qualified per MIL-PRF-38535
- Produced in conformance with Standard Microcircuit Drawing (SMD) [5962-13215](#)

Related Literature

- For a full list of related documents, visit our website - [ISL71590SEH](#), [ISL73590SEH](#) product pages

SEE Test Objectives

The ISL71590SEH was tested to determine its susceptibility to destructive single-event effects including Single-Event Burnout (SEB) and Single-Event Latch-up (SEL). The part is an all-bipolar design, so Single-Event Gate Rupture (SEGR) is not a direct concern; however, the part does contain a poly-oxide-silicon capacitor and Single-Event Dielectric Rupture (SEDR) is a consideration. Nondestructive effects were not characterized as the part operates essentially in a DC environment.

SEE Test Facility

Testing was performed at the Texas A&M University (TAMU) Cyclotron Institute heavy ion facility. This facility is coupled to a K500 super-conducting cyclotron, which is capable of generating a wide range of test particles with the various energy, flux, and fluence levels needed for advanced radiation testing. Four units of the ISL71590SEH were subjected to heavy ion damage testing on June 20, 2013. The units were heated to $+150^\circ\text{C}$ case temperature in order to assure worst-case conditions and were irradiated with gold at zero degrees incidence for an effective surface LET of $86.3\text{MeV}\cdot\text{cm}^2/\text{mg}$.

Since the ISL71590SEH is two-terminal proportional to absolute temperature current source (with a nominal scale factor of $1\mu\text{A}/\text{K}$), the variable used for SEE damage testing was the supply voltage using 2V increments. The normal supply voltage range for the ISL71590SEH is 4V to 33V. In order to determine destructive damage we monitored the supply current, recording the pre- and post-irradiation values. Each sample was irradiated to a fluence of 2×10^6 ions/ cm^2 at a flux of 1×10^4 ions/ $\text{cm}^2\cdot\text{s}$ at each voltage level.

The raw results appear in [Table 1](#). Allowing $\pm 1\mu\text{A}$ of measurement repeatability variation, only two tests (1 and 2 at 39V) appeared to damage the parts. All four parts passed at voltages of 37V and below; this value is 12% above the part's maximum rating.

Conclusion

SEE testing of the ISL71590SEH temperature sensor has demonstrated that the ISL71590SEH and the ISL73590SEH are not susceptible to destructive single-event effects at an LET of $86.3\text{MeV}\cdot\text{cm}^2/\text{mg}$ up to an input voltage of 37V. This represents conditions that are 12% over the recommended maximum input voltage of 33V.

TABLE 1. RESULTS OF DESTRUCTIVE SEE TESTING OF THE ISL71590SEH

UNIT SN	V _{CC} (V)	I _{CC} PRE (μA)	I _{CC} POST (μA)	I _{CC} DELTA (μA)	RESULT
1	31	422	423	1	Pass
2		423	424	1	Pass
3		423	422	-1	Pass
4		420	421	1	Pass
1	33	423	423	0	Pass
2		424	424	0	Pass
3		421	422	1	Pass
4		422	422	0	Pass
1	35	424	423	-1	Pass
2		424	424	0	Pass
3		422	422	0	Pass
4		423	423	0	Pass
1	37	424	424	0	Pass
2		424	424	0	Pass
3		423	423	0	Pass
4		422	422	0	Pass
1	39	424	427	3	Fail
2		424	2000	1576	Fail
3		423	423	0	Pass
4		423	423	0	Pass

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338