



# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PTA33C	PLBG0112GA-A	BP-112 / BP-112V



The pin1 is located in the hatching portion



Position dimension of cells (mm)	$Z_w$	15.4
	$Z_L$	15.4
	$e_w$	15
	$e_L$	15
Thickness (mm)	$H_1$	8.5
Number of cells	$N_w$	8
	$N_L$	20
Maximum storage No. IC/Tray		160
Maximum storage No. IC/Inner box		1280
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack