




# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT873C	PLQP0176KC-A	FP-176 / FP-176V
	PLQP0176KD-A	FP-176C / FP-176CV
	PLQP0216LB-A	FP-216 / FP-216V

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	$Z_W$	27.1
	$Z_L$	25.25
	$e_W$	40.8
	$e_L$	37.9
	$S_W$	55
Thickness (mm)	$H_1$	7.6
	$H_2$	2.5
Number of cells	$N_W$	3
	$N_L$	8
Maximum storage No. IC/Tray		24
Maximum storage No. IC/Inner box		240
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack