


# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
M095-65	PLQP0116JA-A	116P6A-A
	PLQP0176LA-A	176P6R-A

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	$Z_w$	22.3
	$Z_L$	24
	$e_w$	27
	$e_L$	28
Thickness (mm)	$H_1$	5.6
Number of cells	$N_w$	5
	$N_L$	10
Maximum storage No. IC/Tray		50
Maximum storage No. IC/Inner box		250
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C MAX
Packing form		Dry pack