




CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT491B	PRQP0056JB-C	FP-56CV

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	Z_W	17.9
	Z_L	27.9
	e_w	25
	e_L	20
	S_w	25
Thickness (mm)	H_1	7.6
	H_2	2.5
Number of cells	N_W	5
	N_L	14
Maximum storage No. IC/Tray		70
Maximum storage No. IC/Inner box		700
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Non dry pack