


CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
M095-23B	PRQP0080GB-B	80P6N-C
	PRQP0100JB-A	100P6S-A
	PRQP0100JB-B	100P6S-C
	PRQP0100JC-A	100P6P-E

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	Z_w	20.3
	Z_L	24.9
	e_w	22.4
	e_L	27.8
Thickness (mm)	H_1	6.4
Number of cells	N_w	6
	N_L	10
Maximum storage No. IC/Tray		60
Maximum storage No. IC/Inner box		300
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C MAX
Packing form		Dry pack