


JEDEC TRAY

Tray Code	RENESAS Code	Previous Code
SL-BG060615TJ-1	PTLG0064JA-A	64F0G
	PTLG0077KA-A	77F0E
	PTLG0113KA-A	113F0E
	PWQN0020GA-A	20PJZ-A
	PWQN0036KA-B	36PJW-B
	PWQN0040KB-A	40PJS-A

Unit:mm



The pin1 is located in the hatching portion

Note : Numbers in parentheses are the numbers of ICs contained in five trays per inner box, and those without parentheses are the numbers of ICs contained in eight trays per inner box.

Position dimension of cells (mm)	Z_w	8.15
	Z_L	7.9
	e_w	9.2
	e_L	8.8
Thickness (mm)	H_1	7.62
Number of cells	N_w	14
	N_L	35
Maximum storage No. IC/Tray		490
Maximum storage No. IC/Inner box (Note)		4410(2450)
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack