


JEDEC TRAY

Tray Code	RENESAS Code	Previous Code
PTB75C	PLBG0256GA-A	BP-256HV
	PLBG0256GB-A	BP-256B / BP-256BV
	PLBG0336GA-A	BP-336 / BP-336V
	PRBG0256GA-A	—
	PRBG0272GA-A	—
	PRBG0292GA-A	—

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	Z_W	19.2
	Z_L	21
	e_W	19.5
	e_L	19.5
Thickness (mm)	H_1	7.62
Number of cells	N_W	6
	N_L	15
Maximum storage No. IC/Tray		90
Maximum storage No. IC/Inner box		720
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack