

May 16, 2012

Main Specifications of the 9.0-inch FHD model

Part number:	NL192108AC10-01D
Resolution:	1920(H) x 1080(V) pixels
Display area:	198.72(H) x 111.78(V) mm Diagonal screen size of 9.0-inches (23cm)
Drive system:	Amorphous-silicon TFT active-matrix
Display color:	16.77M colors
Pixel arrangement:	RGB vertical stripe
Pixel pitch:	0.1035(H) x 0.1035(V) mm
Luminance:	400 cd/m ² (typ.) *at IL=TBD mA
Viewing angle:	Vertical : Up 88 degrees, down 88 degrees Horizontal : Right 88 degrees, left 88 degrees (Contrast ratio at over 10:1)
Color gamut:	72% (NTSC ratio)
LED Driver Circuit	Built-in