



| SYMBOL | DIMENSION IN MM | | | DIMENSION IN INCH | | |
|--------|-----------------|-------|-------|-------------------|-------|-------|
| | MIN. | NOM | MAX. | MIN. | NOM | MAX. |
| A | | | 1.20 | | | 0.047 |
| A1 | 0.05 | | 0.15 | 0.002 | | 0.006 |
| A2 | 0.95 | 1.00 | 1.05 | 0.037 | 0.039 | 0.041 |
| b | 0.30 | | 0.45 | 0.012 | | 0.018 |
| △ b1 | 0.30 | 0.35 | 0.40 | 0.012 | 0.014 | 0.016 |
| c | 0.12 | | 0.21 | 0.005 | | 0.008 |
| △ c1 | 0.12 | 0.15 | 0.16 | 0.005 | 0.006 | 0.006 |
| e | 0.80 BASIC | | | 0.031 BASIC | | |
| D | 18.28 | 18.41 | 18.54 | 0.720 | 0.725 | 0.730 |
| E | 11.56 | 11.76 | 11.96 | 0.455 | 0.463 | 0.471 |
| E1 | 10.03 | 10.16 | 10.29 | 0.395 | 0.400 | 0.405 |
| L | 0.40 | 0.50 | 0.60 | 0.016 | 0.020 | 0.024 |
| L1 | 0.25 BASIC | | | 0.010 BASIC | | |
| R | 0.12 | | 0.25 | 0.005 | | 0.010 |
| △ θ | 0 | | 8 | 0 | | 8 |
| θ1 | 10 | 15 | 20 | 10 | 15 | 20 |
| △ N | 44L | | | | | |
| JEDEC | MO-133(BA) | | | | | |

NOTE: DIMENSIONS D AND E1 DO NOT INCLUDE MOLD PROTRUSIONS.

D AND E1 ARE MAXIMUM PLASTIC BODY SIZE DIMENSIONS INCLUDING MOLD MISMATCH.

| Package Revision History | | |
|--------------------------|---------|-----------------|
| Date Created | Rev No. | Description |
| June 28, 2020 | 00 | Initial Release |
| | | |