


NOTE :

- 1. DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS 0.25 MM. PER SIDE AND MAXIMUM PLASTIC BODY SIZE DIMENSIONS INCLUDING MOLD MISMATCH.
- 2. LEAD WIDTH DIMENSION DOES NOT INCLUDE DAMBER PROTRUSION.
- 3. THIS PART REFERENCE JEDEC DRAWING NO. MS-026 VARIATION ACD.
- 4. FOOT LENGTH IS MEASUREMENT AT GAGE PLANE 0.25 MM ABOVE SEATING PLANE.
- 5. LEAD SPAN/STAND OFF HEIGHT/COPLANARITY ARE CONSIDERED AS SPECIAL CHARACTERISTIC(S)
- 6. COO & CAVITY ID ARE INCLUDED IN PIN#1 IDENTIFICATION.
- 7. CONTROLLING DIMENSION IN MM.



EPAD 5.3 mm SQ

Package Revision History		
Date Created	Rev No.	Description
4/29/21	00	Initial Release