





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	4/28/16	JH
01	UPDATE DRAWING	8/30/16	JH



SYMBOL	DIMENSION		
	MIN.	NOM.	MAX.
A	0.55	0.60	0.65
A3	0.25	0.30	0.35
b	0.39	0.44	0.49
L	0.49	0.54	0.59
D	2.125	2.200	2.275
E	1.925	2.00	2.075
E1	1.25	1.30	1.35
e	0.80 BSC		
K	0.08 TYP		
ccc	0.02		



- NOTES:
1. ALL DIMENSIONING AND TOLERANCING CONFORM TO ANSI Y14.5M-1982
 2. ALL DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES UNLESS SPECIFIED DECIMAL ANGULAR ±1° XX± XXX± XXXX±		 www.IDT.com 6024 Silver Creek Valley Road San Jose CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591	
APPROVALS	DATE	TITLE LAG6 PACKAGE OUTLINE	
DRAWN RALC	4/28/16	2.2 x 2.0 x 0.60 mm BODY	
CHECKED		0.80 mm PITCH ODFNP	
		SIZE C	DRAWING No. PSC-4658
		DO NOT SCALE DRAWING	REV 01
			SHEET 1 OF 1