



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	27.0	—
E	—	27.0	—
v	—	—	0.20
w	—	—	—
A	—	—	2.5
A <sub>1</sub>	0.5	0.6	0.7
e	—	1.27	—
b	0.60	0.75	0.90
x	—	—	0.30
y	—	—	0.20
y <sub>1</sub>	—	—	0.35
S <sub>D</sub>	—	0.635	—
S <sub>E</sub>	—	0.635	—
Z <sub>D</sub>	—	—	—
Z <sub>E</sub>	—	—	—