





256-PIN PLASTIC BGA (27x27)



ITEM	MILLIMETERS
A	27.00±0.20
B	24.0
C	24.0
D	27.00±0.20
E	1.44
F	1.27 (T.P.)
G	0.6±0.1
H	0.36
I	1.53±0.15
J	2.13±0.25
K	0.15
L	$\phi 0.75 \pm 0.15$
M	0.30
N	0.10
P	C3.95
R	25°
S	1.5

Y256S1-127-B6-1