


352-PIN PLASTIC BGA (35x35)



NOTE

Each ball centerline is located within $\phi 0.30$ mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	35.00±0.15
B	32.50
C	32.50
D	35.00±0.15
E	1.62
F	1.27 (T.P.)
G	0.60±0.05
H	0.56
I	1.73±0.10
J	2.33±0.25
K	0.15
L	$\phi 0.75 \pm 0.15$
M	0.30
P	C0.7
R	25°
S	1.25