



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	27	—
E	—	27	—
v	—	—	0.20
w	—	—	0.3
A	—	—	2.6
A_1	0.4	0.5	0.6
e	—	1.0	—
b	0.5	0.6	0.7
x	—	—	0.10
y	—	—	0.15
y_1	—	—	0.35
Z_D	—	1.0	—
Z_E	—	1.0	—
D_1	—	24	—
E_1	—	24	—