



636-PIN PLASTIC BGA (27x27)



ITEM	MILLIMETERS
D	27.00±0.20
D1	24.00
E	27.00±0.20
E1	24.00
w	0.30
e	1.00
A	2.23±0.20
A1	0.50±0.10
A2	1.73
b	0.60±0.10
x	0.10
y	0.15
y1	0.35
ZD	1.00
ZE	1.00

P636F1-100-MNQ