


<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>Previous Code</b>	<b>MASS (Typ) [g]</b>
P-FBGA272-17x17-0.80	PRBG0272GB-A	—	0.90

Unit: mm



Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	—	17.00	—
D1	—	15.20	—
E	—	17.00	—
E1	—	15.20	—
v	—	—	0.15
w	—	—	0.20
e	—	0.80	—
A	—	1.58	2.00
A1	0.30	0.35	0.40
b	0.49	0.54	0.59
x	—	—	0.08
y	—	—	0.10
y1	—	—	0.20
ZD	—	0.90	—
ZE	—	0.90	—