



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	19	—
E	—	19	—
v	—	—	0.15
w	—	—	0.2
A	—	—	1.9
A_1	0.35	0.4	0.45
e	—	0.8	—
b	0.45	0.5	0.55
x	—	—	0.08
y	—	—	0.1
y_1	—	—	0.2
S_D	—	—	—
S_E	—	—	—
Z_D	—	1.1	—
Z_E	—	1.1	—