



433-PIN PLASTIC FBGA (17x17)



(UNIT:mm)

| ITEM | DIMENSIONS |
|------|------------|
| D | 17.00±0.10 |
| E | 17.00±0.10 |
| w | 0.20 |
| e | 0.65 |
| A | 1.81±0.09 |
| A1 | 0.30±0.05 |
| A2 | 1.51 |
| b | 0.40±0.05 |
| x | 0.08 |
| y | 0.10 |
| y1 | 0.20 |
| ZD | 1.025 |
| ZE | 1.025 |

P433F1-65-GN3