



624-PIN PLASTIC BGA (FLIP CHIP TYPE) (27x27)



(UNIT:mm)

ITEM	DIMENSIONS
D	27.00±0.10
D1	26.10±0.05
E	27.00±0.10
E1	26.10±0.05
w	0.30
e	1.00
A	3.00±0.40
A1	0.45±0.10
A2	2.55
b	0.60±0.10
x	0.10
y	0.20
y1	0.35
ZD	1.50
ZE	1.50

P624F5-100-MN2-1