




672-PIN PLASTIC BGA (CAVITY DOWN TYPE) (45x45)



ITEM	MILLIMETERS
A	45.00±0.20
B	22.5
C	22.5
D	45.00±0.20
E	1.545
F	1.27 (T.P.)
G	0.60±0.10
H	1.88
J	2.48±0.30
K	0.15
L	φ0.75±0.15
M	0.30
N	0.25 MIN.
P	0.10

S672S2-127-K6-3