

JEITA Package Code

RENESAS Code

Previous Code



MASS[Typ.]

P-HFBGA560-25x25-0.80

PRBG0560GA-A

560F7S

2.3g



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	25.0	—
E	—	25.0	—
v	—	—	0.15
w	—	—	0.20
A	—	—	2.6
A_1	0.3	0.35	0.4
e	—	0.8	—
b	0.4	0.45	0.5
x	—	—	0.08
y	—	—	0.12
y_1	—	—	0.20
Z_D	—	1.7	—
Z_E	—	1.7	—
D_1	13.9	14.0	14.1
E_1	13.9	14.0	14.1