

外形図 Outline drawing
 Renesasコード PLQP0176KH-B



RDK-G-001784

1/1

ルネサスエレクトロニクス株式会社
 Renesas Electronics Corporation


JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-HLFQFP176-24x24-0.50	PLQP0176KH-B	1.97

UNIT: MM




NOTE)



1. DIMENSION 'D1' & 'E1' DO NOT INCLUDE MOLD FLASH.
2. LEAD WIDTH 'b' DOES NOT INCLUDE TRIM OFFSET.



DETAIL F



SECTION B-B'



Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
A	—	—	1.60
A ₁	0.05	—	0.15
A ₂	—	1.40	—
D	25.80	26.00	26.20
D ₁	23.80	24.00	24.20
E	25.80	26.00	26.20
E ₁	23.80	24.00	24.20
N	—	176	—
e	—	0.50	—
b	0.17	0.22	0.27
b ₁	0.17	0.20	0.23
c	0.09	—	0.20
c ₁	0.09	—	0.16
θ	0°	—	7°
L	0.45	0.60	0.75
L ₁	—	1.00	—
D2	—	6.20	—
E2	—	6.20	—
ccc	—	—	0.08
ddd	—	—	0.08