





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-HLQFP100-14x20-0.65	PLQP0100JB-B	100P6K-B	1.2g



Detail F

NOTE)
 1. DIMENSIONS $**1*$ AND $**2*$ DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION $**3*$ DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	19.9	20.0	20.1
E	13.9	14.0	14.1
A ₂	—	1.4	—
H _D	21.8	22.0	22.2
H _E	15.8	16.0	16.2
A	—	—	1.7
A ₁	0.05	0.125	0.2
b _p	0.27	0.32	0.37
c	0.105	0.125	0.175
θ	0°	—	8°
Ⓢ	—	0.65	—
x	—	—	0.13
y	—	—	0.10
L	0.35	0.5	0.65
D ₂	—	15.0	—
E ₁	—	9.0	—