


JEITA Package Code
P-HLQFP40-7x7-0.65

RENESAS Code
PLQP0040JC-A

Previous Code
—

MASS[Typ.]
0.18g



NOTE)
1. DIMENSIONS *1 AND *2 DO NOT INCLUDE MOLD FLASH
2. DIMENSION *3 DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	6.90	7.00	7.10
E	6.90	7.00	7.10
A ₂	—	1.40	—
H _D	8.80	9.00	9.20
H _E	8.80	9.00	9.20
A	—	—	1.70
A ₁	0.00	—	0.15
b _p	0.2	0.24	0.28
c	0.10	0.15	0.20
θ	0°	—	8°
ⓔ	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z _D	—	0.575	—
Z _E	—	0.575	—
L	0.4	0.5	0.6