

JEITA Package Code

RENASAS Code

Previous Code

MASS[Typ.]

P-HSSOP36-11x14.1-0.65






PRSP0036JA-A

FP-36DT/FP-36DTV


2.05g

NOTE)

1. DIMENSIONS**1"AND**2"
DO NOT INCLUDE MOLD FLASH.
2. DIMENSION**3"DOES NOT
INCLUDE TRIM OFFSET.



Terminal cross section



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	13.95	14.1	14.25
E	10.9	11.0	11.1
A_2	—	—	—
A_1	0.01	0.05	0.10
A	—	—	3.6
b_p	0.27	0.32	0.37
b_1	0.26	0.30	0.34
c	0.28	0.32	0.37
c_1	0.26	0.30	0.34
θ	0°	—	8°
H_E	14.0	14.2	14.4
e	—	0.65	—
x	—	—	0.25
y	—	—	0.1
Z	—	—	—
L	0.65	0.8	0.95
L_1	—	—	—