


<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>Previous Code</b>	<b>MASS (Typ) [g]</b>
P-HVQFN32-5x5-0.50	PVQN0032KF-A	—	0.05

Unit: mm



Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	4.90	5.00	5.10
E	4.90	5.00	5.10
A	—	—	1.00
A <sub>1</sub>	0.00	—	—
b	0.20	0.25	0.30
e	—	0.50	—
L <sub>P</sub>	0.30	0.40	0.50
x	—	—	0.05
y	—	—	0.05
Z <sub>D</sub>	—	0.75	—
Z <sub>E</sub>	—	0.75	—
c	—	0.20	—
D <sub>2</sub>	—	3.50	—
E <sub>2</sub>	—	3.50	—