

JEITA Package Code

RENESAS Code

Previous Code






MASS[Typ.]

P-HWQFN20-4x4-0.50

PWQN0020KA-A

20PJW-A

0.03g



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	3.9	4.0	4.1
E	3.9	4.0	4.1
A <sub>2</sub>	—	0.75	—
A	—	—	0.8
A <sub>1</sub>	0	0	0.05
b <sub>p</sub>	0.15	0.2	0.25
e	—	0.5	—
L <sub>p</sub>	0.5	0.6	0.7
x	—	—	0.05
y	—	—	0.05
Z <sub>D</sub>	—	1.0	—
Z <sub>E</sub>	—	1.0	—
D <sub>2</sub>	—	2.26	—
E <sub>1</sub>	—	2.26	—