



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	13.00	—
E	—	13.00	—
v	—	—	0.15
w	—	—	0.20
A	—	—	1.40
A ₁	0.28	0.33	0.38
e	—	0.65	—
b	0.35	0.40	0.45
x	—	—	0.08
y	—	—	0.10
y ₁	—	—	0.2
S _D	—	—	—
S _E	—	—	—
Z _D	—	0.65	—
Z _E	—	0.65	—