



### 304-PIN PLASTIC FBGA (19x19)



ITEM	MILLIMETERS
A	19.00±0.10
B	18.40
C	18.40
D	19.00±0.10
E	1.10
F	0.8 (T.P.)
G	0.35±0.1
H	0.36
I	1.16
J	1.51±0.15
K	0.10
L	$\phi 0.50^{+0.05}_{-0.10}$
M	0.08
P	C1.0
Q	R0.3
R	25°
W	0.20
Y1	0.20

S304S1-80-6C-1