



401-PIN PLASTIC FBGA (14x13)



(UNIT:mm)

| ITEM | DIMENSIONS |
|------|------------|
| D | 14.00±0.10 |
| E | 13.00±0.10 |
| v | 0.15 |
| w | 0.20 |
| e | 0.50 |
| SD | 0.25 |
| SE | 0.25 |
| A | 1.28±0.10 |
| A1 | 0.22±0.05 |
| A2 | 1.06 |
| b | 0.30±0.05 |
| x | 0.05 |
| y | 0.08 |
| y1 | 0.20 |
| ZD | 0.75 |
| ZE | 0.75 |

P401F1-50-EP1-1