




| | | | |
|--------------------|--------------|---------------|------------|
| JEITA Package Code | RENESAS Code | Previous Code | MASS[Typ.] |
| P-LFPGA49-6x6-0.80 | PLBG0049GA-A | 49FHE | 0.1g |



| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|------|------|
| | Min | Nom | Max |
| D | — | 6.0 | — |
| E | — | 6.0 | — |
| v | — | — | 0.15 |
| w | — | — | 0.20 |
| A | — | — | 1.4 |
| A ₁ | 0.3 | 0.35 | 0.4 |
| E | — | 0.8 | — |
| b | 0.4 | 0.45 | 0.5 |
| x | — | — | 0.08 |
| y | — | — | 0.10 |
| Z _D | — | 0.6 | — |
| Z _E | — | 0.6 | — |