




JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-LFQFP256-28x28-0.40	PLQP0256LB-A	FP-256B/FP-256BV	2.7g



NOTE)
 1. DIMENSIONS**1**AND**2**
 DO NOT INCLUDE MOLD FLASH
 2. DIMENSION**3**DOES NOT
 INCLUDE TRIM OFFSET.



Terminal cross section



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	27.9	28	28.1
E	27.9	28	28.1
A ₂	—	1.40	—
H _D	29.8	30.0	30.2
H _E	29.8	30.0	30.2
A	—	—	1.70
A ₁	0.05	0.10	0.15
b _p	0.13	0.18	0.23
b ₁	—	0.16	—
c	0.095	0.145	0.195
c ₁	—	0.125	—
θ	0°	—	8°
[e]	—	0.4	—
x	—	—	0.07
y	—	—	0.08
Z _D	—	1.40	—
Z _E	—	1.40	—
L	0.4	0.5	0.6
L ₁	—	1.0	—