




外形図 Outline drawing
 Renesasコード PLQP0048KK-A

RDK-G-001665 1/1

ルネサス エレクトロニクス株式会社
 Renesas Electronics Corporation

JEITA Package Code	RENESAS Code	MASS(Typ.)[g]
P-LFQFP48-7×7-0.50	PLQP0048KK-A	0.18



Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
A	—	—	1.60
A ₁	0.05	—	0.15
A ₂	1.35	1.40	1.45
D	—	9.00	—
D ₁	—	7.00	—
E	—	9.00	—
E ₁	—	7.00	—
N	—	48	—
e	—	0.50	—
b	0.17	0.22	0.27
c	0.09	—	0.20
θ	0°	3.5°	7°
L	0.45	0.60	0.75
L ₁	—	1.00	—
aaa	—	—	0.20
bbb	—	—	0.20
ccc	—	—	0.08
ddd	—	—	0.10