





<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>Previous Code</b>	<b>MASS (Typ) [g]</b>
P-LFQFP144-16x16-0.40	PLQP0144LA-A	—	0.90



Unit: mm



NOTE)  
 1. DIMENSIONS "\*\*1" AND "\*\*2"  
 DO NOT INCLUDE MOLD FLASH.  
 2. DIMENSION "\*\*3" DOES NOT  
 INCLUDE TRIM OFFSET.

Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	15.9	16.0	16.1
E	15.9	16.0	16.1
A <sub>2</sub>	—	1.4	—
H <sub>D</sub>	17.8	18.0	18.2
H <sub>E</sub>	17.8	18.0	18.2
A	—	—	1.7
A <sub>1</sub>	0.05	0.10	0.15
b <sub>p</sub>	0.13	0.18	0.23
b <sub>1</sub>	—	0.16	—
c	0.09	0.145	0.20
c <sub>1</sub>	—	0.125	—
$\theta$	0°	—	8°
e	—	0.4	—
x	—	—	0.07
y	—	—	0.08
Z <sub>D</sub>	—	1.0	—
Z <sub>E</sub>	—	1.0	—
L	0.35	0.5	0.65
L <sub>1</sub>	—	1.0	—