





JEITA Package Code	RENASAS Code	Previous Code	MASS[Typ.]
P-QFJ44-16.58x16.58-1.27	PRQJ0044DB-A	CP-44/CP-44V	2.0g



Terminal cross section



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	16.58	—
E	—	16.58	—
H_D	17.40	17.53	17.66
H_E	17.40	17.53	17.66
A_1	—	0.90	—
A	4.20	4.40	4.60
b	0.33	0.43	0.53
b_1	—	0.38	—
b_2	—	0.74	—
c	—	—	—
c_1	—	—	—
e	—	1.27	—
x	—	—	0.30
y	—	—	0.10
L	2.40	2.55	2.70
e_{1D}	15.00	15.50	16.00
e_{1E}	15.00	15.50	16.00
Z_D	—	1.94	—
Z_E	—	1.94	—