





| | | | |
|--------------------|--------------|---------------|------------|
| JEITA Package Code | RENESAS Code | Previous Code | MASS[Typ.] |
| P-QFP44-10x10-0.80 | PRQP0044GA-A | 44P6N-A | 0.6g |



NOTE)
 1. DIMENSIONS *1* AND *2* DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION *3* DOES NOT INCLUDE TRIM OFFSET.

| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|------|------|
| | Min | Nom | Max |
| D | 9.8 | 10.0 | 10.2 |
| E | 9.8 | 10.0 | 10.2 |
| A_2 | — | 2.8 | — |
| H_D | 12.5 | 12.8 | 13.1 |
| H_E | 12.5 | 12.8 | 13.1 |
| A | — | — | 3.05 |
| A_1 | 0 | 0.1 | 0.2 |
| b_D | 0.3 | 0.35 | 0.45 |
| c | 0.13 | 0.15 | 0.2 |
| θ | 0° | — | 10° |
| e | — | 0.8 | — |
| x | — | — | 0.20 |
| y | — | — | 0.10 |
| Z_D | — | 1.0 | — |
| Z_E | — | 1.0 | — |
| L | 0.4 | 0.6 | 0.8 |