


## 40-PIN PLASTIC SOJ (10.16mm(400))



### NOTE

Each lead centerline is located within 0.12 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
B	26.29 <sup>+0.20</sup> <sub>-0.35</sub>
C	10.16±0.1
D	11.18±0.2
E	1.08±0.15
F	0.7
G	3.5±0.2
H	2.4±0.2
I	0.8 MIN.
J	2.6±0.1
K	1.27(T.P.)
M	0.42 <sup>+0.08</sup> <sub>-0.07</sub>
N	0.12
P	9.40±0.20
Q	0.15
T	R0.85
U	0.22 <sup>+0.08</sup> <sub>-0.07</sub>

P40LE-400A-4