

JEITA Package Code

RENESAS Code

Previous Code




MASS[Typ.]

P-SOP10-5.7x6.8-1.27

PRSP0010DB-A

10P2N-A

0.2g



Detail F

NOTE)

1. DIMENSIONS "*1" AND "*2" DO NOT INCLUDE MOLD FLASH.
2. DIMENSION "*3" DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	6.7	6.8	6.9
E	5.6	5.7	5.8
A ₂	—	1.8	—
A ₁	0	0.1	0.2
A	—	—	2.1
b _p	0.35	0.4	0.5
c	0.18	0.2	0.25
θ	0°	—	8°
H _E	7.82	8.12	8.42
e	1.12	1.27	1.42
y	—	—	0.1
L	0.3	0.5	0.7