





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-SOP32-11.4x20.75-1.27	PRSP0032DF-A	32P2S-A	1.3g



Detail F

NOTE)
 1. DIMENSIONS *1* AND *2* DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION *3* DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	20.55	20.75	20.95
E	11.3	11.4	11.5
A2	—	2.75	—
A1	0	0.1	0.2
A	—	—	3.05
bp	0.35	0.4	0.5
c	0.13	0.15	0.2
θ	0°	—	8°
HE	13.8	14.1	14.4
e	—	1.27	—
x	—	—	0.10
y	—	—	0.15
Zb	—	0.85	—
L	0.6	0.8	1.0