


Terminal cross section  
(Ni/Pd/Au plating)



Detail F

NOTE)

1. DIMENSIONS\*<sup>1</sup> (Nom)\*AND\*<sup>2</sup> DO NOT INCLUDE MOLD FLASH.
2. DIMENSION\*<sup>3</sup> DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	5.65	5.85
E	—	5.30	—
A <sub>2</sub>	—	—	—
A <sub>1</sub>	0.102	0.14	0.254
A	—	—	1.73
b <sub>p</sub>	0.35	0.40	0.45
b <sub>1</sub>	—	—	—
c	0.15	0.20	0.25
c <sub>1</sub>	—	—	—
θ	0°	—	10°
H <sub>E</sub>	8.00	8.10	8.20
e	—	1.27	—
x	—	—	0.25
y	—	—	0.1
Z	—	—	1.02
L	0.40	0.60	0.80
L <sub>1</sub>	—	1.40	—